

T18R5-10K2



Article Number: 111-01772

Standard Cable Tie, 4" Long, 18lb Tensile Strength, PA66, Green/White Striped, 50/pkg

 **RoHS**



[Download spec sheet](#)

Base Data

Local Order Number	T18R5-10K2
Type	T18R
Color	Green (GN)
Features and Benefits	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are availableto ensure consistent and safe installation.
Short Description	Standard Cable Tie, 4" Long, 18lb Tensile Strength, PA66, Green/White Striped, 50/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	18.0 lbs
Minimum Tensile Strength (Metric)	80.0 N
Length L (Imperial)	4.0 "
Length L (Metric)	100.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.1 "
Width W (Metric)	2.45 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	0.86 "
Bundle Diameter Max. (Metric)	22.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	50
Carton Quantity	10000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139 MIL 53421
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No