

T50R2M4UL



Article Number: 111-00515

Standard Cable Tie, 8" Long, 50lb Tensile Strength, PA66, Red, 1000/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

|                       |                                                                                                                                                                                                                                                                                                                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Local Order Number    | T50R2M4UL                                                                                                                                                                                                                                                                                                                                                                            |
| Type                  | T50R                                                                                                                                                                                                                                                                                                                                                                                 |
| Color                 | Red (RD)                                                                                                                                                                                                                                                                                                                                                                             |
| Features and Benefits | <ul style="list-style-type: none"><li>• Inside serrations allow for strong hold on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul>                                                                                                               |
| Product Description   | HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are availableto ensure consistent and safe installation. |
| Short Description     | Standard Cable Tie, 8" Long, 50lb Tensile Strength, PA66, Red, 1000/pkg                                                                                                                                                                                                                                                                                                              |

Product Dimensions

|                                     |                 |
|-------------------------------------|-----------------|
| Minimum Tensile Strength (Imperial) | 50.0 lbs        |
| Minimum Tensile Strength (Metric)   | 225.0 N         |
| Length L (Imperial)                 | 8.0 "           |
| Length L (Metric)                   | 202.0 mm        |
| Fixation Method                     | None            |
| Identification Plate Position       | none            |
| Releasable Closure                  | No              |
| Tie Closure                         | plastic pawl    |
| Variant                             | Inside Serrated |
| Width W (Imperial)                  | 0.18 "          |
| Width W (Metric)                    | 4.6 mm          |
| Bundle Diameter Min. (Imperial)     | 0.06 "          |
| Bundle Diameter Min. (Metric)       | 1.5 mm          |
| Bundle Diameter Max. (Imperial)     | 1.97 "          |
| Bundle Diameter Max. (Metric)       | 50.0 mm         |

Logistics and Packaging

|                           |      |
|---------------------------|------|
| Quantity Per              | bag  |
| Package Quantity (Metric) | 1000 |
| Carton Quantity           | 5000 |

Material and Specifications

---

|                                      |                                                    |
|--------------------------------------|----------------------------------------------------|
| <b>Material</b>                      | Polyamide 6.6 (PA66)                               |
| <b>Material Shortcut</b>             | PA66                                               |
| <b>US MILSPEC</b>                    | MS3367-1-2                                         |
| <b>Flammability</b>                  | UL94 V2                                            |
| <b>Halogenfree</b>                   | Yes                                                |
| <b>Operating Temperature</b>         | -40°F to +185°F (-40°C to +85°C)                   |
| <b>ROHS Compliant</b>                | Yes                                                |
| <b>Certification/Specification</b>   | Cage Code 53421<br>UL-ZODZ E64139<br>SAE - AS33671 |
| <b>UL Listed (US and Canada)</b>     | Yes                                                |
| <b>UL Recognized (US and Canada)</b> | Yes                                                |