

ACCS1001

APC Rack Air Containment Rear Assembly for NetShelter SX 42U and InRow 600mm



Purchase

Purchase



ACCS1001

Overview

Model Name	APC Rack Air Containment Rear Assembly for NetShelter SX 42U and InRow 600mm
Includes	Installation guide
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Andorra, United Arab Emirates, Afghanistan, Antigua And Barbuda, Anguilla, Albania, Armenia, Netherlands Antilles, Angola, Argentina, Austria, Australia, Aruba, Azerbaijan, Bosnia And Herzegovina, Barbados, Bangladesh, Belgium, Burkina Faso, Bulgaria, Bahrain, Burundi, Benin, Bermuda, Brunei Darussalam, Bolivia, Brazil, Bahamas, Bhutan, Botswana, Belarus, Belize, Canada, CONGO, THE DEMOCRATIC REPUBLIC OF THE, Central African Republic, Congo, Switzerland, Cote D'Ivoire, Cook Islands, Chile, Cameroon, China, Colombia, Costa Rica, Serbia And Montenegro, Cuba, Cyprus, Czech Republic, Germany, Djibouti, Denmark, Dominica, Dominican Republic, Algeria, Ecuador, Estonia, Egypt, Western Sahara, Spain, Ethiopia, Finland, Fiji, Falkland Islands (Malvinas), France, Gabon, United Kingdom, Grenada, Georgia, French Guiana, Ghana, Gibraltar, Gambia, Guinea, Guadeloupe, Equatorial Guinea, Greece, Guatemala, Guyana, Hong Kong, Honduras, Croatia, Haiti, Hungary, Indonesia, Ireland, Israel, India, Iraq, Iran (Islamic Republic Of), Iceland, Italy, Jamaica, Jordan, Japan, Kenya, SAINT KITTS AND NEVIS, KOREA, REPUBLIC OF, Kuwait, Cayman Islands, Kazakhstan, Lebanon, SAINT LUCIA, Liechtenstein, Sri Lanka, Liberia, Lesotho, Lithuania, Luxembourg, Latvia, Morocco, Moldova, Republic Of, Madagascar, Macedonia, Mali, Myanmar, Martinique, Mauritania, Malta, Mauritius, Maldives, Oman, Panama, Peru, Papua New Guinea, Philippines, Pakistan, Poland, Puerto Rico, Portugal, Paraguay, Reunion, Romania, Russian Federation, Rwanda, Saudi Arabia, Sudan, Sweden, Singapore, Slovenia, Slovakia (Slovak Republic), Sierra Leone, Senegal, Somalia, El Salvador, Turks And Caicos Islands, Chad, Togo, Thailand, Turkmenistan, Tunisia, East Timor, Turkey, Trinidad And Tobago, Taiwan, TANZANIA, UNITED REPUBLIC OF, Ukraine, Uganda, United States, Uruguay, Uzbekistan, SAINT VINCENT AND THE GRENADINES, Venezuela, VIRGIN ISLANDS (UNITED STATES), Viet Nam, Yemen, Mayotte, South Africa, Zambia, Zimbabwe

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Physical

Maximum Height	1911 mm
Maximum Width	600 mm
Maximum Depth	196 mm
Net Weight	21.5 kg
Shipping Weight	29.59 kg
Shipping Height	152 mm
Shipping Width	508 mm
Shipping Depth	2032 mm
Color	Black

Conformance

Standard Warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

Other Environmental Compliance	China RoHS
--------------------------------	------------