VANDAL RESISTANT



CIS8 Series

INTERCOM ASSEMBLY 2-Gang Listen-Only Stat on, Vandal Resistant, Stainless Steel, NO But on

GENERAL DESCRIPTION

The **OS8Series** is a 2-gang, vandal resistant 'listen-only' stat on consist ng of a 2.5" square frame loudspeaker with a 2.35 oz. ceramic magnet & phenolic impregnated, moisture resistant cone

Three (3) intervoven, steel security screens are mounted between the 12 guage brushed stainless steel faceplate and loudspeaker. Tamper resistant, 6-32 x 1" 'pin-in-torx' hardware included.

MODELS AVAILABLE

CIS8/8	8 Ohm Speaker
CIS8/25	1W-25V, 3-Tap Transformer (1W, 0.5W, 0.25W)
CIS8/45	45 Ohm Speaker

INTENDED USE - Indoor or Protected Outdoor Environment

Program Material Signal Tones and Voice

AUDIO SPECIFICATIONS


Average Sensit vity 87 dB SPL, 1W/1M Frequency Response Nominal Coverage Angle Audio Connect on


Magnet Type & Weight BeFe Ceramic, 2.35 oz. Nominal 200 Hz - 8 kHz EIA 426A Standard 90° Included Angle, -6 dB / 2 kHz, Half space 25V: 7" Color-Coded Leads, Pre-Cut 8 & 45 Ohm: 0.205' Spade Terminal

RECOMMENDED QUAM COMPONENTS

Enclosures | Surface Mount : SE7GVP, SE8GVP, SE9GVP







Recommended construct on sequences, installat on instruct ons, and A&E Specificat ons are available in various formats in the QUAM Architects' and Engineers' Resources sect on on the web at: www.QuamSpeakers.com

© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without not ce.





QUAM-NICHOLS COMPANY, INC. 234 East Marquet e Rd. Chicago, IL. 60637 Tel: 1-800-NEED-NOW (800-633-3669) Fax: 1-888-NEED-NOW (888-633-3669) e-mail: NeedNovv@QNC.com www.QuamSpeakers.com