

Z440 EE Management Workstation

www.boschsecurity.com



BOSCH

Invented for life



- ▶ Highest-performance workstation with Intel's next-generation microarchitecture
- ▶ Four-monitor support (AMD FirePro W7100, 8 GB graphics card)
- ▶ Silent running with HP low acoustics chassis
- ▶ Protected by HP Services, including a 3 years Next Business Day on-site support

This HP Z440 management workstation with its latest processing and I/O power from Intel, and the latest graphics technology from leading graphics providers is designed for video-oriented applications that require high performance and most advanced visualization. HP Z440 features a sleek 4U chassis with built-in handles that offers tool-less access to the inside and easy configurability for seamless deployment. This brand new tool-free chassis boasts low acoustics and single integrated Gigabit Ethernet to deliver whisper-quiet performance. HP Z440 is built to minimizing power and cooling costs with ENERGY STAR qualified configurations featuring 90% efficient power supplies while taking on bigger computing challenges with the latest Intel vPro technology and the next generation Intel Xeon six-core processor:

- Intel Xeon E5-1650 v3 (3.5 GHz, 15 MB cache, 2133 MHz memory speed, Six-Core, HT, Turbo)
- 8 GB (2 x 4 GB) DDR4 2133 ECC Registered Memory

HP Z440 is a workstation solution based on the Intel C612 Chipset using Intel's vPro technology and on 8 DIMM slots in 4-channel memory architecture.

With 2 x PCI Express Gen3 x16, 1 x PCI Express Gen3 x8, 1 x PCI Express Gen2 x4, 1 x PCI Express Gen2 x1 and 1 x Legacy PCI slots, HP Z440 delivers high performance bandwidth interfaces and future expandability:

- The architecture of this management workstation delivers next generation I/O throughput to achieve high throughput and visualization requirements.
- The ultra high-end AMD FirePro W7100 (8 GB, 4 x Display Ports, max. resolution 4096 x 2160 at 24 bpp 60 Hz) 3D graphics card ensures highest performance and resolution for fast presentation of displayed video data.

System overview

Z440 EE Management Workstation is the highest-performance workstation suitable for running the security systems software applications offered by Bosch.

Please refer to the respective application data sheets to get detailed information.

Intel Microarchitecture offers the latest in processor innovation, including:

- Design and performance scalability with **Intel Hyper-Threading Technology** (Intel HT Technology), scalable cache sizes, system interconnects, and integrated memory controllers.
- **Intel Turbo Boost Technology** delivers additional performance automatically when needed by taking advantage of the processor's power and thermal headroom. Intel Xeon E5-1650 v3 with 1.3 turbo boost stepping (3.8 GHz max).
- Intel Hyper-Threading Technology brings high-performance applications into mainstream computing with 1 - 16+ threads optimized for new generation multi-core processor architecture. Intel Xeon E5-1650 v3 provides up to 12 threads.
- **Intel vPro Technology** for maximized, hardware-assisted security and manageability.

Certifications and approvals

RoHS	Compliant with the European Union's Restrictions of Hazardous Substances (RoHS) Directive 2011/65/EU
WEEE	Designed to comply with the Waste Electrical and Electronic Equipment (WEEE) Directive—2002/96/EC
ISO 11469 ISO 1043	Plastic parts used in the product weighing over 25 g are marked per ISO 11469 and ISO 1043
	Contains 0% recycled materials (by weight)
	Product is >90% recyclable when properly disposed of at end-of-life

Approvals

Region	Certification	
Europe	CE	Z440 Declaration of Conformity

Installation/configuration notes

Language selection

This management workstation comes in four standard localizations:

MHW-WZ4R4-EEDE German localization/keyboard

MHW-WZ4R4-EEUK British English localization/keyboard

MHW-WZ4R4-EERU Russian localization/keyboard

MHW-WZ4R4-EEUS American English localization/keyboard

Additional optional keyboards listed under **Ordering Information** are available.



Notice

The Bosch management workstation comes with Microsoft Windows 8 pre-installed. If Windows 7 Professional is required as OS the **Windows 7 Downgrade Option** must be ordered together with the management workstation. If this option is ordered the shipment will contain the Windows 7 DVD media kit only, the workstation will still come with Windows 8 pre-installed.



Notice

The Bosch management workstation provides a MUI (Multilingual User Interface) option. The language of the workstation selected during initial installation may be changed at any point in time during operations according to Microsoft Windows 8 guidelines.

Parts included

Quantity	Components
1	HP Z440 8-DIMM Workstation
1	• HP Z440 localization kit (see supported language)
1	• HP Z440 700 W, 90% efficient chassis
1	• 500 GB, 7200 RPM SATA, 1st HDD
1	• HP USB standard keyboard
1	• HP USB optical scroll mouse
1	• HP 9.5 mm slim blue-ray writer SATA, 1st ODD
1	• Intel Xeon E5-1650 v3 (3.5 GHz/15 MB/2133 6C CPU)
1	• 8 GB (2 x 4 GB) DDR4-2133 Registered RAM
1	• AMD FirePro W7100 graphics card (8 GB, 4 x display ports)
1	• HP serial port adapter kit
1	Microsoft Windows 8.1 Professional Edition, 64-bit OS
1	HP 3-year Next Business Day on-site hardware support



Notice

The Next Business Day on-site service level can only be provided if the respective system has been registered within eight weeks after receipt. Otherwise, service will be provided based on best effort.

Information about registration details is available in every shipment (registration form) or from the Bosch online product catalogue.

Next Business Day Services cannot be provided in every country everywhere. For limitations and exceptions see the registration details in the registration form.

Technical specifications

Electrical	
Power supply	700 W, 90% efficient, custom PSU (wide ranging, active Power Factor Correction)
Operating voltage range	90 to 269 VAC
Rated voltage range	100 to 240 VAC
	118 VAC
Rated line frequency	50/60 Hz (at 100 to 240 VAC)
	400 HZ (at 118 VAC)
Operating line frequency range	47 to 66 Hz (at 100 to 240 VAC)
	393 to 407 HZ (at 118 VAC)
Rated input current	100 to 240 V at 9.5 A
	118 V at 9.5 A
Power consumption in sleep mode (as defined by ENERGY STAR) - Suspend to RAM (S3) (instantly available PC)	<15 W
Heat dissipation (configuration and software dependent)	1648 BTU/h typical (415 kcal/h)
	2746 BTU/h max (692 kcal/h)
Power supply fan	92 x 25 mm variable speed
ENERGY STAR qualified	Yes
80 PLUS compliant	Yes, 90% efficient
FEMP standby power compliant at 115 V (<2 W in S5 – power off)	Yes
EuP compliant at 230 V	Yes
Mechanical	
Form factor	Rackable minitower
Chassis dimensions	
• Standard minitower orientation (H x W x D)	43.2 x 16.9 x 44.5 cm (17.0 x 6.65 x 17.5 in)
• Rack dimensions	4U
Environmental	
Temperature	
• operating	5 °C to 35 °C (40 °F to 95 °F)

Environmental	
• non-operating	-40 °C to 60 °C (-40 °F to 140 °F)
Humidity	
• operating	8 to 85% relative humidity, non-condensing
• non-operating	8 to 90% relative humidity, non-condensing
Maximum altitude (non-pressurized)	
• operating	3,048 m (10,000 feet)
• non-operating	9,144 m (30,000 feet)

Notes:

- General technical specifications for the workstation are provided in the HP Z440 QuickSpecs (DA-15077 Worldwide QuickSpecs - Version 5 - 2.1.2015).
- Configuration specifications are supplied in the Parts Included section.

Hewlett Packard and the HP logo are registered trademarks of Hewlett Packard, all rights reserved. All data and dimensions are referenced from the Hewlett Packard QuickSpecs and are subject to change without notice.

Intel is a registered trademark of Intel; Xeon, Core and vPro are trademarks of Intel, all rights reserved.

NVIDIA Quadro is a registered trademark of NVIDIA, all rights reserved.

AMD FirePro is a registered trademark of Advanced Micro Devices Inc., all rights reserved.

Energy Star is a registered trademark of U.S. Environmental Protection Agency, all rights reserved.

80 PLUS is a registered trademark of Ecos, all rights reserved.

Ordering information

Z440 EE Management Workstation DE

Highest-performance workstation. German
Order number **MHW-WZ4R4-EEDE**

Z440 EE Management Workstation UK

Highest-performance workstation. British English
Order number **MHW-WZ4R4-EEUK**

Z440 EE Management Workstation RU

Highest-performance workstation. Russian
Order number **MHW-WZ4R4-EERU**

Z440 EE Management Workstation US

Highest-performance workstation. American English
Order number **MHW-WZ4R4-EEUS**

Accessories

Windows 7 Downgrade Option

Windows 7, 64-bit professional edition media kit. This option has to be ordered together with the initial order of a workstation; it cannot be ordered as a stand-alone item.

Order number **MHW-AWDGO-WIN7**

Localization CH

Localization (Keyboard): Switzerland—French/German

Order number **MHW-AWLCK-SUI**

Localization CZ

Localization (Keyboard): Czech Republic—Czech

Order number **MHW-AWLCK-CZ**

Localization DK

Localization (Keyboard): Denmark—English

Order number **MHW-AWLCK-DK**

Localization ES

Localization (Keyboard): Spain—Spanish

Order number **MHW-AWLCK-ESP**

Localization FR

Localization (Keyboard): France—French

Order number **MHW-AWLCK-FR**

Localization IT

Localization (Keyboard): Italy—Italian

Order number **MHW-AWLCK-IT**

Localization NL

Localization (Keyboard): Netherlands—Dutch

Order number **MHW-AWLCK-NL**

Localization NO

Localization (Keyboard): Norway—Norwegian

Order number **MHW-AWLCK-NO**

Localization SV

Localization (Keyboard): Sweden—Swedish

Order number **MHW-AWLCK-SE**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
203 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com