

MHW-WZ2R0-EL Management Workstation

www.boschsecurity.com



BOSCH
Invented for life



- ▶ Entry-level workstation with next-generation Intel® Core™ i3 series processors
- ▶ Integrated Intel HD Graphics (dual-monitor support)
- ▶ Protected by HP Services, including a 3 years Next Business Day on-site support

This HP Z200 management workstation offers an entry-point into the Bosch video-oriented applications that require entry-level performance and visualization by offering the advanced power and productivity of HP's latest workstation technology at a rivaling price point. HP Z200 is engineered to optimize the way the processor, memory, graphics, operating systems, and software work together.

Though HP Z200 comes at an entry-level price point it offers reliable enterprise-class technology—including ECC memory that helps ensure data integrity and higher system uptime.

Get fast performance with built-in memory controller and the latest Intel® Core™ i3 dual-core processor:

- Intel® Core™ i3-540 Processor (3.06 GHz, 4 MB cache, 1333 MHz memory, Dual-Core, HT)
- 4 GB (2 x 2 GB) DDR3-1333 ECC Unbuffered RAM

Save energy with ENERGY STAR® 5.0 qualification, 89% efficient power supplies, and HP WattSaver technology, which, when activated, consumes less than 1 W in off mode.

HP Z200 is a workstation solution based on the Intel® PCH 3450 Chipset offering one additional PCIe x16 Gen2 slot as well as 1 PCIe x16 Gen1, 1 PCIe x1 Gen1, 1 PCIe x4 Gen1, and 3 PCI slots for future expandability.

The integrated Intel HD Graphics provides onboard graphics functionality without requiring an additional graphics card.

With a smart new chassis it is easy to access—both inside and out with a tool-free chassis and two convenient USB ports on the front. The convertible minitower chassis allows for Minitower or Desktop orientation.

System Overview

MHW-WZ2R0-EL Management Workstation is the entry-level workstation suitable for running the security systems software applications offered by Bosch. Please refer to the respective application data sheets to get detailed information.

Dual-Core Intel® (Clarkdale) processor for HP Z200:

- Design and performance scalability with Intel® Hyper-Threading Technology (Intel® HT Technology), scalable cache sizes, system interconnects, and integrated memory controllers
- Intel® Hyper-Threading Technology brings high-performance applications into mainstream computing optimized for a new generation multi-core processor architecture

Integrated Intel® HD Graphics:

- Unified Memory Architecture (UMA)—a region of system memory is reserved and dedicated to the graphics display
- DirectX 10.0 compliant
- 2D/3D graphics core
- 1 Single-link DVI-I and 1 DP (Display Port) graphics ports integrated in motherboard—integrated graphics can do dual display across DP and DVI-I

Certifications and Approvals

RoHS	Compliant with the Restrictions of Hazardous Substances (RoHS) directive—2002/95/EC
WEEE	Designed to comply with the Waste Electrical and Electronic Equipment (WEEE) Directive—2002/96/EC
ISO 11469 ISO 1043	Plastic parts used in the product weighing over 25 g are marked per ISO 11469 and ISO 1043
	Contains 0% recycled materials (by weight)
	Product is >90% recyclable when properly disposed of at end-of-life

Region	Certification	
Global	DOC	Z200 Declaration of Conformity (CE + UL)
	RoHS	HP Compliance with RoHS directives

Installation/Configuration Notes

Application package

MHW-WZ2R0-EL Management Workstation can have either the VIDOS or the Bosch VMS application package installed at one time.

Language selection

MHW-WZ2R0-EL base unit does not come with a predefined language but offers a choice of language options. One of the localization kits listed under Ordering Information must be selected when ordering. MHW-WZ2R0-ELUS base unit comes with a US localization kit.



Notice

The Bosch management workstation provides a MUI (Multilingual User Interface). With MUI installed the language of the workstation may be changed after initial installation (for details see document “Installation Note MUI on Bosch Platforms”).

Parts Included

Quantity	Components
1	HP Z200 Workstation
1	• HP Z200 localization kit (select desired language)
1	• HP Z200 320 W, 89% efficient chassis
1	• HP 250 GB SATA 7200, 1st HDD
1	• HP USB standard keyboard
1	• HP USB optical scroll mouse
1	• HP 16X DVD± RW SuperMulti SATA
1	• Intel® Core™ i3-540 (3.06/4 MB/1333 DC CPU)
1	• HP 4 GB (2 x 2 GB) DDR3-1333 ECC RAM
1	• HP integrated graphics
1	Microsoft Windows 7 Ultimate Edition, 64-bit OS
1	HP 3-year Next Business Day on-site hardware support

Technical Specifications

Electrical	
Power supply	320 W, wide ranging, Active Power Factor Correction, 89% efficient
Operating voltage range	90 to 264 VAC
Rated voltage range	No
Rated line frequency	No
Operating line frequency range	No
Rated input current	No
Power consumption in sleep mode (defined by ENERGY STAR®)—suspend to RAM (S3) (instantly available PC)	<5 W
Heat dissipation (configuration and software dependent)	1419 BTU/h typical (358 kcal/h)
	2027 BTU/h max (511 kcal/h)
Power supply fan	92 x 25 mm variable speed
ENERGY STAR® qualified	Yes
80 PLUS compliant	Yes
Mechanical	
Form factor	Convertible minitower
Chassis dimensions (H x W x D) Minitower or desktop orientation	44.76 x 17.78 x 45.43 cm (17.6 x 7 x 17.9 in)
Environmental	
Temperature	

• operating	5 °C to 35 °C (40 °F to 95 °F)
• non-opering	-40 °C to 60 °C (-40 °F to 140 °F)
Humidity	
• operating	8 to 85%
• non-operating	8 to 90%
Maximum altitude (non-pressurized)	
• operating	3,000 m (10,000 feet)
• non-operating	9,100 m (30,000 feet)

Notes:

- General technical specifications for the workstation are provided in the HP Z200 QuickSpecs (Worldwide—Version 12—January 1, 2011).
- Configuration specifications are supplied in the Parts Included section.

Hewlett Packard and the HP logo are registered trademarks of Hewlett Packard, all rights reserved. All data and dimensions are referenced from the Hewlett Packard QuickSpecs and are subject to change without notice.

Intel is a registered trademark of Intel; Core is a trademark of Intel, all rights reserved.

NVIDIA Quadro is a registered trademark of NVIDIA, all rights reserved.

Energy Star is a registered trademark of U.S. Environmental Protection Agency, all rights reserved.

80 PLUS is a registered trademark of Ecos, all rights reserved.

Ordering Information**MHW-WZ2R0-EL Management Workstation**

Entry-level workstation, onboard GC (localization kit must be ordered separately)
Order number **MHW-WZ2R0-EL**

MHW-WZ2R0-ELUS Management Workstation

Entry-level workstation US, onboard GC (US localization kit is included)
Order number **MHW-WZ2R0-ELUS**

Accessories**MHW-AWLCK-CZ**

Localization (Keyboard): Czech Republic—Czech
Order number **MHW-AWLCK-CZ**

MHW-AWLCK-DE

Localization (Keyboard): Germany—German
Order number **MHW-AWLCK-DE**

MHW-AWLCK-DK

Localization (Keyboard): Denmark—English
Order number **MHW-AWLCK-DK**

MHW-AWLCK-ESP

Localization (Keyboard): Spain—Spanish
Order number **MHW-AWLCK-ESP**

MHW-AWLCK-FR

Localization (Keyboard): France—French
Order number **MHW-AWLCK-FR**

MHW-AWLCK-IT

Localization (Keyboard): Italy—Italian
Order number **MHW-AWLCK-IT**

MHW-AWLCK-NL

Localization (Keyboard): Netherlands—Dutch
Order number **MHW-AWLCK-NL**

MHW-AWLCK-NO

Localization (Keyboard): Norway—Norwegian
Order number **MHW-AWLCK-NO**

MHW-AWLCK-RU

Localization (Keyboard): Russia—Russian
Order number **MHW-AWLCK-RU**

MHW-AWLCK-SE

Localization (Keyboard): Sweden—Swedish
Order number **MHW-AWLCK-SE**

MHW-AWLCK-SUI

Localization (Keyboard): Switzerland—French/German
Order number **MHW-AWLCK-SUI**

MHW-AWLCK-UK

Localization (Keyboard): United Kingdom—British English
Order number **MHW-AWLCK-UK**

MHW-AWLCK-US

Localization (Keyboard): USA — American English
Order number **MHW-AWLCK-US**

MHW-AWSP-PCI

HP Serial Port Adapter z-Series (not built-in)
Order number **MHW-AWSP-PCI**

Software Options**MHW-AWDGO-XP**

Windows XP Downgrade Option
Order number **MHW-AWDGO-XP**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
al.securitysystems@bosch.com
www.boschsecurity.com