



106664147 | M30MC-262
Rectangular Mounting Collar, white

General Specifications

Color	White
Mount Type	Snap-in
Product Type	Mounting collar
Total Ports, quantity	1
Application	Fit into a rectangular opening
Package Quantity	100

Dimensions

Depth	11.68 mm		0.46 in
Height	25.40 mm		1.00 in
Width	26.16 mm		1.03 in
Weight	0.00 kg		0.01 lb

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system