

**ARBOSEAL BUTYL 88****DESCRIPTION**

Arboseal Butyl 88 is a round section, preformed butyl strip. It deforms under moderate pressure and has appreciable surface tack and recovery.

**MAIN APPLICATIONS**

Recommended for use in compression joints in roofing and cladding, lap joints in guttering.

**NB:** Not recommended for use in expansion joints.

**HEALTH AND SAFETY**

No known health hazards associated with this product. Please consult Material Safety Data Sheet for full information.

**TECHNICAL DATA**

Application Temperature:	+ 5° C to + 50° C
Service Temperature:	- 25° C to + 50°C
Chemical Resistance:	Fair resistance to most dilute acids and alkalis, vegetable oils and alcohol. Poor resistance to hydrocarbon solvents.
UV Resistance:	Good
Service Life:	20 years+
Colours:	Black

**STORAGE LIFE**

36 months in original unopened packaging stored in a cool, dry place out of direct sunlight

**ACCESSORIES****Cleaners**

Arbo Cleaner No.17- 1 Litre Tin (Xylene based – not suitable for use with plastics or delicate finishes)

Arbo Cleaner No. 16 - 1 Litre Tin (Alcohol Based)

**Packaging:**

Sizes: 6, 8, 10 mm

**Multi-Strand Reels;**

6mm Diameter = 41.3 metres/reel, 4 per box

8mm Diameter = 27 metres/reel, 4 per box

10mm Diameter = 17 metres/reel, 4 per box

**Important:** The information in this leaflet is given in good faith and based on results gained from experience and tests. However, all recommendations or suggestions are made without guarantee since the conditions of use are beyond our control. Goods are supplied subject to the Company's terms and conditions of sales, a copy of which is available on request.

**Arbo sealants are manufactured in the U.K. by Adshead Ratcliffe.**