



Limpet Printed Tapes Limited

**Bond House
Hardwicke Road
Great Gransden
Sandy
Bedfordshire
SG19 3BJ**

Printable PVC Self Adhesive Tape

Technical Specifications

Type of File	PVC	
Width	48mm	
Length	66m, 132m, 1056m	
Film Colour	Transparent	White
Film Thickness	32 $\mu \pm 10\%$	35 $\mu \pm 10\%$
Tensile Strength MD (N/cm)	50 ± 30	
Elongation at Break MD (%)	75 ± 30	
Adhesive	Solvent-based, Natural Rubber	
Colour	Transparent / Brown / White	Transparent / White
Peel Adhesion (N/25mm)	4.0 ± 1	
Shear Adhesion (h,25mm x 25mm on stainless steel, 23°C)	Over 300	
Rolling Ball Tack (cm)	Under 3	

Stocking time

We recommend using the product within 6 months from the delivery

Stocking Conditions

The product has to be stocked in a dry environment, at a temperature around 21°C and 50% relative humidity. The product must be stored protected from dust, humidity and direct sun exposure. It must be stored horizontally and kept in the original packaging

Use

Prior to use, carefully check that the contact surfaces are totally dry and clean from oil, grease and dust.

If the storage temperature has been different from what suggested, bring the tape to the temperature before application

The mentioned data stem from an average analysis carried out on our standard production and may undergo unexpected changes. Therefore they are not binding for our company