



Part Number	I10003 -- MN01X4W1-36PT68-3TL6A0A10-S Upgradeable, Basic
Power Configuration	30A, 208V, 4.9kW
Physical Configuration	72 in / 1829 mm Vertical



Description	The I10003 -- MN01X4W1-36PT68-3TL6A0A10-S basic upgradeable PDU offers robust power delivery as well as a path to upgrade to an intelligent device with power monitoring by plugging in one of Geist's Interchangeable Monitoring Devices (IMD).	
Product Summary	I10003 -- MN01X4W1-36PT68-3TL6A0A10-S - Upgradeable, Basic, 30A, 208V, Vertical, (30) Locking IEC C13,(6) Locking IEC C19, breakered, 10 ft power cord with L6-30P, No Monitoring (Upgradeable with IMD module)	
Monitoring	No Monitoring (Upgradeable with IMD module)	
Plug Form	 L6-30P	
Receptacle	 Locking IEC C13 (Quantity: 30)	 Locking IEC C19 (Quantity: 6)

I10003 -- MN01X4W1-36PT68-3TL6A0A10-S - Product Specification and Options

Monitoring	No Monitoring (Upgradeable with IMD module)
Quantity Of Inputs	1
Voltage	208V
Current	30A
VA per Input (Load Capacity)	4.9kW
Frequency	50/60 Hz
Over Current Protection	(2) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	NEMA L6-30P Twistlock
Combined Total Receptacle/Socket Quantity	36
Receptacle/Socket Type #1	Locking IEC C13
Quantity on Face #1	30
Quantity per Breaker #1	15
Style #1	Individual
Voltage per Receptacle/Socket #1	208V
Receptacle/Socket Type #2	Locking IEC C19
Quantity on Face #2	6
Quantity per Breaker #2	3
Style #2	Individual
Voltage per Receptacle/Socket #2	208V
Continuous Operating Temperature Range	50% derated operation: 45-60C / 113-140F (See product manual or quick-start guide for full de-rated operating conditions)
Continuous Operating Temperature Range	Full nameplate operation: 10-45C / 50-113F
Heavy Steel -Black Powder Coat	Yes
Configuration	72in / 1832mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	Five Year
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	NOM-003-SCFI-2000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	72in x 2in x 2in
Shipped Weight	16lbs (7.26kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2910,

Geist Asia

Hong Kong
Tel: +852 81764860

1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geistglobal.com

No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Email: salesasia@geistglobal.com