



TECHNICAL Practice

TELECOM SOLUTIONS FOR THE 21ST CENTURY

PNL70

**E-70 Replacement
Faceplates**

September 10, 2009

**Update Your E-70 Series Phone to a Unique Faceplate
Finish or Replace an Existing Damaged Faceplate**



PNL70-SS
(Brushed Stainless Steel)



PNL70-BN
(Oil Rubbed Bronze)



PNL70-PB
(Polished Brass)



PNL70-WH
(Satin White)



PNL70-BK
(Fine Texture Satin Black)

The **PNL70** is a replacement faceplate with color matching screws and LED light pipe for the **E-70** Series entry phones.

The **PNL70** is available in several different finishes. All unique colors are coated with an extremely durable U.V. resistant powder paint designed for rugged outdoor use.

Available Finishes

Model	Description
PNL70-SS	Brushed Stainless Steel (similar to brushed nickel)
PNL70-BN	Oil Rubbed Bronze (satin dark brown powder paint with fine copper metallic)
PNL70-PB	Polished Brass with clear gloss powder paint to prevent tarnishing
PNL70-WH	Satin white powder paint (matches Anderson Windows white casing)
PNL70-BK	Fine texture satin black powder paint

Applications

- Use the **PNL70** faceplates with Viking's **E-70** Series entry phones

Specifications

Dimensions: Faceplate: 123.8mm x 125.4mm x 4.3mm (4.875" x 4.938" x 0.17")

Shipping Weight: 0.1 kg (0.2 lbs)

Mounting: #6-32 x 1.25" flat head, 5/64" Hex drive, stainless steel, powder coated to match faceplate

Faceplate Material: **PNL70-SS/BN/WH/BK:** 18 gauge, 0.048" thick 304 stainless steel **PNL70-PB:** 16 gauge 0.050" thick 260 polished brass

Phone...715.386.8861

www.vikingelectronics.com

Product Support Line...715.386.8666

Fax Back Line...715.386.4345

Due to the dynamic nature of the product design, the information contained in this document is subject to change without notice. Viking Electronics, and its affiliates and/or subsidiaries assume no responsibility for errors and omissions contained in this information. Revisions of this document or new editions of it may be issued to incorporate such changes.