

eXtreme® 6+ 110-Style Patch Cords

APPLICATION

Leviton's eXtreme® 6+ 110-style Patch Cords provide consistent Category 6 performance to cross-connect between 110 blocks, or between 110 blocks and patch panels. Available in both T568A and T568B wiring configurations.

FEATURES

- Available in 1-, 2-, 3-, 5-, 7-, 10-foot lengths (custom lengths available).
- Grey strain relief boot on RJ45 cords.
- TIA/EIA channel performance limits the combined length of work area and equipment room cords to 32 feet (10 meters) per TIA/EIA-568-B.

STANDARDS COMPLIANCE

eXtreme 6+ System components meet or exceed the Category 6/Class E requirements for channel level performance per TIA/EIA-568-B and ISO/IEC 11801-B. Components certified per cULus, NOM and ACA requirements.

PHYSICAL SPECIFICATIONS

Dimensions: 1-, 2-, 3-, 5-, 7-, 10-foot lengths
Materials: Plug body is high-impact, fire-retardant plastic rated UL 94V-0. Spring wire contacts are high quality copper-based alloy. The RJ45 plugs are plated with 50 micro-inches of gold, and the 110-style plug has 3 micro-inches minimum, over 100 micro-inches of nickel for lowest electrical contact resistance and maximum life.
Color: Grey

See ELECTRONIC FILES for CAD files (.DXF, .DWG, MS-DOS.EPS) on disk



WARRANTY INFORMATION

For a copy of Leviton product warranties, log on to www.levitonvoicedata.com/warranty.

For ELECTRONIC Typical Specs see (.TXT) file on disk.

TYPICAL SPECIFICATION

The 110-style patch cord shall meet or exceed the requirements for Category 6 described in TIA/EIA-568-B as well as the Class E requirements described in ISO/IEC 11801-B. The cords shall be available in 1-, 2-, 3-, 5-, 7-, 10-foot lengths. All plastics used in construction of the connector bodies shall be fire-retardant with a UL flammability rating of 94V-0.

eXtreme® 6+ 110-Style Patch Cords

PART NUMBERS

Description	Part No.
eXtreme 6+, 110-style Patch Cords, CAT 6, 110 to 110, 4-pair	62240-*S
eXtreme 6+, 110-style Patch Cords, CAT 6, 110 to 110, A-Wiring	6234A-*S
eXtreme 6+, 110-style Patch Cords, CAT 6, 110 to 110, B-Wiring	6234B-*S

*Lengths= (01) 1-foot, (02) 2-foot, (03) 3-foot, (05) 5-foot, (07) 7-foot, (10) 10-foot



For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005
Spec sheets and updates are also available at www.levitonvoicedata.com.

2222 - 222nd St. SE • Bothell, WA 98021 USA
Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available

