

FJZMPMPAD

LazrSPEED[®] 300 MPO (female) to MPO (female), InstaPATCH[®] 360 Pre-terminated Trunk Cable, 12-Fiber, LSZH

Construction Materials

Fiber Type	LazrSPEED [®] 300, 50 µm multimode fiber (OM3)
Total Fibers, quantity	12
Fibers per Subunit, quantity	12
Furcation Color	Aqua

Dimensions

Breakout Length	33 in
Cord Length, maximum	999 ft 999 m
Cord Length, minimum	10 ft 3 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Brand	InstaPATCH [®] 360
Color, connector A	Aqua
Color, connector B	Aqua
Construction Type	InstaPATCH [®] 360 trunk/extension/cross-connect
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Interface, connector A	MPO Female
Interface, connector B	MPO Female
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

N-012-MP-5L-F12 (Product Component—not orderable) — Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber

FJZMPMPAD

POWERED BY

SYSTIMAX®

- CS-5L-MP (Product Component—not orderable) — LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber
- 860366210 (Product Component—not orderable) — LazrSPEED® Low Loss MPO Female 12 Fiber Connector, aqua