

NetShelter™ WX Wallmount Cabinets

APC by Schneider Electric offers a set of NetShelter WX Wallmount IT cabinets in a convenient flat packaged option in multiple heights & depths for remote wall-mounted applications.



Top view

CABLE ACCESS ROOF / BASE

- > Two removable panels provide access or mounting spaces for accessories
- > Up to 8 additional u-spaces for small accessories such as patch panels



Front view

VERTICAL MOUNTING RAILS

- > Simple vertical adjustment with two equipment mounting rails at the front
- > Numbered U positions
- > Adjust to 6 different depth positions
- > U-spaces compatible with any standard 1, 2, or 3U accessory devices



Rear view

WALL MOUNTED

- > Dedicated space for remote IT assets that frees up floor space
- > Secure space to prevent random access to remote IT assets

ACCESSORY MOUNTING U-SPACE

- > Removeable panels provide 4 U spaces top/bottom
- > Standard u-spaces allows accessorizing with any standard 1, 2, or 3U accessory devices such as patch panels, NetBotz



AR8213
Fan tray



FLAT PACKAGED

- > Flat packaged for protection and ease of transport
- In non freight transport options
- > Simple and quick assembly



AR106
6U



AR109
9U



AR112
12U

OTHER FEATURES

- > Static Load Capacity 200 lb
- > Includes hardware kit 24 cage nuts, screws, washers, cage nut tool, screw/torx combo tool
- > APC logo badge & Schneider Electric logo label
- > Perforated front door is reversible
- > Door, sides, roof, and rails are bonded to frame
- > Flat packaged for protection and ease of transport and storage with simple and quick assembly

Description	Part
6U x 24in Wide x 16in Deep NetShelter WX Wallmount Cabinet	AR106
9U x 24in Wide x 16in Deep NetShelter WX Wallmount Cabinet	AR109
12U x 24in Wide x 24in Deep NetShelter WX Wallmount Cabinet	AR112
Accessories specific to AR106, AR109 and AR112	Part
NetShelter WX Roof Fan Tray for AR106, AR109, AR112	AR8213

NetShelter™ WX Swing Out Wallmount Cabinets

APC by Schneider Electric offers a set of NetShelter WX Wallmount IT cabinets on a swing out frame to provide easy access to remote IT assets in a 13U height with two door options.



WALL MOUNTED

- >Double hinge design provides front and rear access to installed equipment
- >Back door is reversible so Wallbox will work in variety of locations



VERTICAL MOUNTING RAILS

- > Adjustable front mounting rails with #12-24 tapped holes or square cage nut holes
- > Fixed rear mounting rails with square cage nut holes
- > U-spaces compatible with any standard 1, 2, or 3U accessory devices



CABLE ACCESS

- >Back door frame has eight openings for cable access
- >Top and bottom access plates can be removed to provide unrestricted cable access



OTHER FEATURES

- >Static Load Capacity 200 lb
- >Smoked, tempered glass front door (AR100)
- >Fully vented front door (AR100HD)
- > Door, sides, roof, and rails are bonded to frame
- >13U spaces
- >Variety of accessories adapt the wallbox to different applications



AR8355

Vent Gland Plates

AR8206ABLK
Fan Kit



AR8359
Caster Kit

Description	Part
6U x 24in Wide x 16in Deep NetShelter WX Wallmount Cabinet with Glass Front Door Black	AR100
9U x 24in Wide x 16in Deep NetShelter WX Wallmount Cabinet with Vented Front Door Black	AR100HD
Accessories specific AR100 and AR100HD	Part
Roof Fan Tray 120V 50/60HZ for NetShelter WX Enclosures	AR8206ABLK
Roof Fan Tray 208/230V 50/60HZ for NetShelter WX Enclosures	AR8207BLK
NetShelter WX Vented Gland Plates	AR8355
NetShelter WX 13U Glass Front Door	AR8356
NetShelter WX 13U Rear Door	AR8358
NetShelter WX Caster Kit	AR8359