

Dominion® KSX II




Consolidated Remote Management, KVM-over-IP and serial access in one box

Dominion KSX II is an integrated, hardware-based solution that offers you secure, remote KVM (keyboard, video and mouse) access, serial device management and power control. Targeted at branch and remote offices, the Dominion KSX II is also ideal for labs, computer rooms and data centers with racks containing both serial-and KVM-controlled devices. With Dominion KSX II, you'll reduce travel costs, decrease downtime, increase productivity and increase security.

Features and Benefits


- One consolidated view of all IT equipment connected to the KSX II
- A single, platform-independent solution offering centralized, integrated and secure control
- Supports servers with VGA, DVI, HDMI and DisplayPort videocards
- BIOS-level KVM-over-IP control of computers or servers, console-level control of serial devices and remote power control
- Virtual media, giving users the ability to install software, run hardware diagnostics, transfer files and more
- Absolute Mouse Synchronization™, which reduces installation time and sets a new standard for mouse synchronization
- Network-independent access via a built-in modem for emergency access



Secure, remote, out-of-band access and power control of up to 16 network devices over IP

Raritan's Dominion KSX II is designed specifically to make the management of your IT infrastructure at branch locations faster, easier, simpler and more cost-effective. This innovative device combines secure BIOS-level KVM over IP, console-level access and power control (when used with Dominion PX) of everything in your remote server rooms. This means that from anywhere you have access to the Web, you can directly access, troubleshoot and even reboot all of your remote equipment.

Dominion KSX II Model	Description	Dimensions (WxDxH)	Weight	Power and Heat Dissipation
DKSX2-144	4-port KVM, 4-port serial, 2 power control ports, and built-in modem	439mm x 290mm x 44mm 17.3" x 11.4" x 1.75";	3.86kg; 8.51lbs	Single Power 100V/240V 50/60Hz 0.6A
DKSX2-188	8-port KVM, 8-port serial, 2 power control ports, and built-in modem		3.92kg; 8.64lbs	
Computer Interface Modules (CIMs)				
D2CIM-DVUSB	Dual USB, VGA CIM for BIOS virtual media and advanced features	D2CIM-DVUSB-DVI	Dual USB, DVI-D CIM for BIOS virtual media and advanced features	
D2CIM-VUSB	USB CIM for virtual media and Absolute Mouse Synchronization	D2CIM-DVUSB-HDMI	Dual USB, HDMI CIM for BIOS virtual media and advanced features	
DCIM-PS2	CIM for PS/2	D2CIM-DVUSB-DP	Dual USB, DisplayPort CIM for BIOS virtual media and advanced features	
DCIM-SUN	CIM for Sun	DCIM-USBG2	CIM for USB and Sun USB	
Specifications for All Dominion KSX II Models				
Form Factor	1U, full width, rack mountable (brackets included)			
Operating Temperature	0°C - 40°C (32°F - 104° F)			
Remote Connection Network Modem Protocols	Dual 10/100/1000 gigabit Ethernet access (RJ45) with failover. Dual stack IPv4/IPv6 Integrated 56K V.90 (RJ11 port) modem TCP/IP, UDP, RADIUS, LDAP, SNMP v2 and v3, SNTP, DHCP, PAP, CHAP, HTTP, HTTPS			
Local Admin Port (VGA) Keyboard/Mouse Local Admin Port (Serial)	HD15(F) VGA USB(F), 1 USB front, 3 USB rear DB9(M) RS232			
Sample Video Resolutions	640x480, 720x400, 800x600, 1024x768, 1152x864, 1152x900, 1280x1024, 1440x900, 1680x1050 1600x1200,1920x1080			
Warranty	Two years. In addition, Raritan offers two years extended warranty.			



Endorser of the EU Code of Conduct on Data Centre Energy Efficiency

Formulated by the EU's Joint Research Centre, the Code is a measured response to the energy challenges the EU faces. It's aim is to encourage companies with data centers to reduce energy consumption while ensuring business objectives continue to be met.

As an endorser, Raritan have pledged to implement the Code's ethos through devising products and services that help organizations to bring their data centers into line with its best practice recommendations.

Call +31 (0)10 284 4040 or visit www.raritan.eu

Raritan is a proven innovator of power management solutions, DCIM software, and KVM-over-IP for data centers of all sizes. Based in Somerset, NJ, Raritan has a global presence across 38 offices, serving 76 countries and 50,000 locations worldwide. Raritan's award-winning hardware and software solutions increase energy efficiency, improve reliability, and raise productivity. For more information, please visit www.raritan.eu or call +31 (0)10 284 4040.

© 2014 Raritan Inc. All rights reserved. Raritan®, Know more. Manage smarter.™ are registered trademarks or trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners.