



Meets ANSI/BHMA A156.9 B22201 and A156.14 D2781.

227 Flush Pull

- Contoured for ease of pulling.
- Extra deep well.
- Deluxe quality.
- Made from wrought brass.

Dimensions

3-5/8" High x 1-3/4" Wide x 9/16" Deep

Finishes

Ives Number	B3	B4	B5	B10	B10B	B15	B26	B26D
BHMA	605	606	609	612	613	619	625	626



Meets ANSI/BHMA A156.14 D2801.

230 Sliding Door Edge Pull

- 3/4" width allows installation on narrow as well as standard doors.
- Spring automatically returns lever flush with plate.
- Made from solid brass.

Dimensions

3-7/8" High x 3/4" Wide

Finishes

Ives Number	B3	B4	B5	B10	B10B	B15	B26	B26D
BHMA	605	606	609	612	613	619	625	626



42 Pocket Sliding Door Bolt

- Exclusive Ives design permits emergency release of bolt from outside the door.
- Spring activated design allows feather-touch action.
- Brass grommet supplied to cap release hole, protecting the door's finish.
- Made from wrought brass.

Dimensions

Overall Size Plate: 3-1/16" High x 1-5/32" Wide

Strike: 1" High x 3/4" Wide

Depth of Mortise: 5/8"

Finishes

Ives Number	B3	B4	B5	B10	B10B	B15	B26	B26D
BHMA	605	606	609	612	613	619	625	626

A
Hinges & Pivots

B
Pulls & Plates

C
Flush Bolts & Coordinators

D
Latches, Catches & Bolts

E
Stops

F
Exterior Hardware

G15
Miscellaneous Hardware