

R K & J Jones Limited

timber preservatives • wood oils • coatings • decorating sundries

telephone 01842 828101 fax 01842 828171 email sales@birdbrand.co.uk website www.birdbrand.co.uk

SPECIFICATIONS

Product: White Spirit

Test	Method	Result	Limits
Density 15 °C g/ml	ASTMD-1298/4052	0, 7790	0, 7700- 0, 8000
Appearance 25 °C	Visual	Clear & Bright	Clear & Bright
Colour Saybolt	ASTMD-156	>+30	>+30
Flash Point °C (P/M)	ASTMD-93	45	>= 41
Sulphur ppm WT	ASTM D-4045	<10	<=10
Copper Corrosion (3H @50 °C)	ASTM D-130	1a	1
Doctor Test	ASTM D-235	Negative	Negative
Distillation °C	ASTM D-86		
IBP		162	>=150
DBP		199	<=205
Residue % mg/100 ml	ASTMD-1353	0,5	<=1, 3
Benzene % (m/m)	ASTM D-2600	<0, 01	<0, 01
Aromatics % (v/v)	ASTM-D-1319	20, 0	>=16 <= 20