



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART#	DESCRIPTION	WEIGHT
NK6X88M**	8 POSITION, 8 WIRE UNIVERSAL MODULE. MODULE IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.495 LB/100 PCS (678g/100 PCS)

NOTES :


1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. MATERIAL:
MODULE - ABS/PC
RETENTION CAP - ABS
3. ALL CATEGORY 6A, 8 POSITION, 8 WIRE CONNECTOR MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ACTUAL SIZE



R	7-25-14	BJN	LPH	LPH	RELEASED TO PRODUCTION	02341-07
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

PART NUMBER		NK6X88M**	
TITLE			
NETKEY CATEGORY 6A PUNCHDOWN JACK MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME			
M02341CD/00			
DATASET FILE NAME			
M02341CD_DC11/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03 [.8] ANGLES ±		MATERIAL: SEE NOTE 2	
		THIRD ANGLE PROJECTION	
DRAWING NUMBER:		02341 - 11	
DRAWN BY	DATE	CHK	SIZE
BJN	7-25-14	LPH	ONE
SHT 1 OF 1		A	