





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT	SPLIT SLEEVE TYPE
CMDJLC**	.10 lbs/10 Pcs [44.1 g/10 Pcs]	PHOS BRONZE
CMDJAQLC**		
CMDJLCZ**	.10 lbs/10 Pcs [43.7 g/10 Pcs]	ZIRCONIA
CMDJAQLCZ**		

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR OF MODULE BASE, AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. MATERIALS:
 - a. MODULE BASE: ABS
 - b. ADAPTER HOUSING: PLASTIC
 - c. SPLIT SLEEVE: SEE TABLE
 - d. DUST CAP: PLASTIC
4. COMPATIBLE WITH TIA/EIA-604-10 (FOCIS-10) AND TIA/EIA-568B.3
5. DIMENSIONS IN BRACKETS ARE METRIC [mm]

										MINI-COM LC SENIOR/JUNIOR DUPLEX FIBER OPTIC ADAPTER MODULE CUSTOMER DRAWING			
											 TM CORP. TINLEY PARK, ILL 60477		
											 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES	
												DRAWING FILENAME M00948AK_DC_00B.prt	
												SCALE NONE	
										DRAWN BY MC	REVIEW DRAWING NUMBERS		
										DATE 06-26-03	SEE NOTES		
1	03-11-05	MC		RELEASED TO PRODUCTION	00948-18						PART NO. SEE TABLE		
											DRAWING NO. 00948-18		
											SIZE A		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D KWR			