

2



1



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICFPHSE2**	.67 LB/10 PCS (306.0 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
 - FACEPLATE
 - CLEAR SCREW COVER
 - COLOR COORDINATED SCREW COVER
 - CLEAR LABEL COVER
 - MOUNTING SCREW



PART NUMBER		UICFPHSE2**	
TITLE		MINI-COM ULTIMATE ID 2 POSITION HORIZONTAL SLOPED EXECUTIVE SERIES FACEPLATE CUSTOMER DRAWING	
ITEM REVISION NAME		M01288BE/07	
DATASET FILE NAME		M01288BE_DC/07A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XX ± .03 [.8] .XXX ± .010 [.3] ANGLES ±		 THIRD ANGLE PROJECTION	
MATERIAL:		ABS	DRAWING NUMBER: 01288-09
DRAWN BY		JSP	
DATE		7-24-02	SHT 1 OF 1
CHK		JAJP	
SCALE		NONE	SIZE A
DESCRIPTION		ECN	

1	5-14-14	BJN	JSP	MMR	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	01288-09
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2

1

D10100DA/14