




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PART NUMBER | PRINT ON AREA COLOR | APPLICATION DIAMETER RANGE | MATERIAL | "A" +/- .062 LENGTH | "B" +/- .062 PRINT ON AREA | "D" +/- .062 LENGTH | LABELS/CASSETTE |
|-------------|---------------------|----------------------------|----------|---------------------|----------------------------|---------------------|-----------------|
| R100X075VIC | WHITE | .120"-.160" | GMH6 | .75 [19.1] | .25 [6.4] | 1.25 [31.8] | 150 |
| R100X125VIC | | .160"-.220" | | 1.25 [31.8] | .38 [9.5] | 1.75 [44.5] | 100 |
| R100X150VIC | | .220"-.280" | | 1.50 [38.1] | .50 [12.7] | 2.00 [50.8] | |
| R100X150V2C | BLUE | | | | | | |
| R100X150V3C | GREEN | | | | | | |
| R100X150V7C | RED | | | | | | |
| R100X150V8C | YELLOW | | | | | | |
| R100X225VIC | WHITE | .280"-.390" | | 2.25 [57.2] | .75 [19.1] | 2.75 [69.9] | |
| R100X225V2C | BLUE | | | | | | |
| R100X225V3C | GREEN | | | | | | |
| R100X225V7C | RED | | | | | | |
| R100X225V8C | YELLOW | | | | | | |

NOTES:

1. DIMENSION IN [] ARE IN MILLIMETERS.
2. SEE B20393 FOR INSTALLATION INSTRUCTIONS.



CAD FILENAME/LAYERS 100693GQ-DC-C10783/09C

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
TURN TELL ROTATABLE SELF-LAMINATING LABEL
PI CASSETTE, R***X***V*C

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (.XXX) ± .025
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|---------|-----|-----|---|------|---|------|-----|
| 2 | 9/28/11 | RVU | | ADD NEW PN: R100X150V*C AND R100X225V*C. ADD PRINT ON AREA COLOR COLUMN. | 6527 | R | | |
| 1 | 9/24/09 | RVU | | DRAWING RELEASE. | 5845 | R | | |
| 0 | 9/10/09 | RVU | | VOID | | | | |

DRAWN BY
RVU
DATE
09/1/09
CHK'D

MAT'L:
SEE TABLE

SCALE
NTS
DRAWING NO.
C10783
DWG
A
SIZE