



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE MFG. DWG. NO. A61318.
2. DIMENSIONS IN [] ARE IN
MILLIMETERS.



PANDUIT PART NO.	MATERIAL	"A"	"B"	"C"	"D"	LABELS/ROLL
C061X030F JC	WHITE POLYESTER GMP0	0.85 [21.59]	0.610 [15.49]	0.300 [7.62]	0.625 [15.88]	500
C125X030F JC	WHITE POLYESTER GMP0	0.63 [16.00]	0.300 [7.62]	1.250 [31.75]	1.500 [38.10]	200
C188X030F JC	WHITE POLYESTER GMP0	0.63 [16.00]	0.300 [7.62]	1.875 [47.63]	2.125 [53.98]	150
C200X100F JC	WHITE POLYESTER GMP0	1.13 [28.70]	1.000 [25.40]	2.000 [50.80]	2.250 [57.15]	150
C252X030F JC	WHITE POLYESTER GMP0	0.63 [16.00]	0.300 [7.62]	2.520 [64.01]	2.875 [73.03]	125
C261X030F JC	WHITE POLYESTER GMP0	0.63 [16.00]	0.300 [7.62]	2.610 [66.29]	2.875 [73.03]	125
C315X030F JC	WHITE POLYESTER GMP0	0.63 [16.00]	0.300 [7.62]	3.150 [80.01]	3.500 [88.90]	100
C379X030F JC	WHITE POLYESTER GMP0	0.63 [16.00]	0.300 [7.62]	3.790 [96.27]	4.125 [104.78]	75

										PANDUIT
										CORP TINLEY PARK, ILLINOIS
										CUSTOMER DRAWING
										LS8 COMPONENT LABELS
										C***X***FJC
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
										(.X) ± (.XXX) ± .015 (.XX) ± .030 ANGLES ±
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
									DRAWN BY RVU	MAT'L: SEE TABLE
O	5-11-06	RVU		DRAWING RELEASE	4503	R			DATE 5-11-06	SCALE NTS
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	DWG SIZE C10413 B