

**CommScope—Proprietary and Confidential. Preliminary specifications are for illustrative purposes only and will be updated prior to publication.**

760028373 | Cat 6 16V

**Entrance Protector, continuity only, no protection, for 302, 303, and 308 connector blocks**

## Dimensions

Depth	36.07 mm   1.42 in
Height	107.95 mm   4.25 in
Width	107.95 mm   4.25 in

## Electrical Specifications

ANSI/TIA Category	6
Clamping Voltage	16 V
Response Time, maximum	5 ns
Response Time, minimum	2 ns

## Environmental Specifications

Safety Standard	UL
-----------------	----

## General Specifications

Product Type	Entrance protector
Application	Data
Body Style	Short
Color	Red
Ground Wire Gauge Require, isolated	14 AWG
Ground Wire Gauge Require, primary	10 AWG
Grounding Connection	Integral shield grounding clip attaches to cable
Package Quantity	1
Protector Type	Solid state

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

