



107067860 | M20AP-246
M20 Dust Cover for M-Series Faceplates and Outlets, ivory

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Product Type	Cover
Color	Ivory
Package Quantity	100

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

Antenna Input Dimensions

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

