



108168543 | M14L-262

**L Type Flush Mounted Faceplate, four port white**

- Available for use with the DYMO® labeling solution

## General Specifications

Color	White
Mount Type	Flush
Product Type	Flush mount modular faceplate
Total Ports, quantity	4
Application	Used with M-Series modular information outlet
Package Quantity	1

## Dimensions

Depth	7.37 mm   0.29 in
Height	115.82 mm   4.56 in
Width	71.37 mm   2.81 in
Weight	0.04 kg   0.08 lb

## Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

## Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system