



108258450 | M10LW-246

Wall Mount Telephone, one port ivory

- Available for use with the DYMO® labeling solution

General Specifications

Color	Ivory
Mount Type	Flush
Product Type	Flush mount modular faceplate
Total Ports, quantity	1
Application	Used with M-Series modular information outlet
Package Quantity	1

Dimensions

Depth	7.37 mm 0.29 in
Height	115.82 mm 4.56 in
Width	71.37 mm 2.81 in
Weight	0.04 kg 0.08 lb

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system