



760049445 | VP360-4U-32P  
**VisiPatch® 360 4U Patch Panel Kit**

## Dimensions

Depth	287.02 mm		11.30 in
Height	180.34 mm		7.10 in
Width	215.90 mm		8.50 in

## Electrical Specifications

ANSI/TIA Category	6A
-------------------	----

## Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	Austel   CE   cUL   UL

## General Specifications

Product Design	VisiPatch® 360
Product Type	Panel
Brand	VisiPatch® 360
Includes	Back panel   Four label holders   Four wiring block covers   Four wiring blocks   Thirty-two connecting blocks   Twelve white labels
Package Quantity	1

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

