

760117911 | MFC-LCF-09-5X-25

LazrSPEED® Fiber Qwik II-LC Connector™, field installable, aqua, 25 Pack



## Construction Materials

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber (OM2+)   LazrSPEED® 300, 50 µm multimode fiber (OM3)   LazrSPEED® 550, 50 µm multimode fiber (OM4)
Ferrule Geometry	Factory polished
Ferrule Material	Zirconia

## Dimensions

Compatible Cable Diameter	0.9 mm   0.0 in
Length	42.60 mm   1.68 in

## General Specifications

Interface	LC
Body Style	BTW
Interface Feature	Field Installable   Mechanical splice
Color	Aqua
Package Quantity	25

## Mechanical Specifications

Cable Retention Strength, maximum	0.45 kg @ 0 ° 1.00 lb @ 0 °
-----------------------------------	--------------------------------

## Optical Performance

Insertion Loss, typical	0.27 dB
Return Loss, minimum	20.0 dB
Insertion Loss Change, mating	0.20 dB
Insertion Loss Change, temperature	0.30 dB

## Optical Specifications

Optical Components Standard	ANSI/TIA-568-C.3
-----------------------------	------------------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

---

Insertion Loss Change, mating      Maximum insertion loss change after 500 matings  
Insertion Loss Change, temperature      Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)