

This specification is OBSOLETE



760144477 | SPL DR FAN 115V 24IN
Split Door Fan 115V 600 mm (24 inches)

OBSOLETE

This product was discontinued on: December 31, 2014

Dimensions

Depth	66.0 mm 2.6 in
Height	298.0 mm 11.7 in
Width	500.0 mm 19.7 in
Weight	4.50 kg 9.92 lb

Electrical Specifications

Current	0.21 A
Input Energy	14.5 W
Power Frequency	60 Hz
Voltage	115 Vac
Voltage, startup	65 Vac

General Specifications

Ordering Note	Available in Mexico, Central America, and South America Available in the United States and Canada
Cabinet Type	Network cabinet Server cabinet
Product Type	Fan
Color	Black
Finish	Powder-coated, textured
Package Quantity	2

Mechanical Specifications

Fan Capacity	102 ft ³ /min
Material Type	Steel

Packed Dimensions

Shipping Weight	4.50 kg 9.92 lb
-----------------	-------------------

760144477 | SPL DR FAN 115V 24IN

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

