



760152827 | HGS-A-KS-BK
High Density Keystone Adapter, bulk pack

Dimensions

Depth	21.84 mm		0.86 in
Height	3.56 mm		0.14 in
Width	12.70 mm		0.50 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Product Type	Adapter
Color	Black
Brand	SYSTIMAX®
Ordering Note	Minimum order quantity, 20 packs
Package Quantity	25

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

