



760152876 | HGS-TT-S
Hand Termination Tool, seat only

Dimensions

Depth	127.00 mm		5.00 in
Height	33.02 mm		1.30 in
Width	25.40 mm		1.00 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Product Type	Tool
Brand	SYSTIMAX®
Ordering Note	Minimum order quantity, 20 packs
Package Quantity	10

Mechanical Specifications

Material Type	Zinc
---------------	------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

