

# STI METAL PROTECTIVE CABINETS



STI-7560



STI-EM151804



STI-EM111504



STI-EM121204



STI-EM07123.5



STI-EM111103



STI-EM08073.5



## PRODUCT OVERVIEW

These enclosures for electrical and electronic equipment (up to 1000V) provide personal protection from hazardous parts and provides a degree of protection to enclosed equipment. EM models are constructed for indoor use. All enclosures offer protection against vandalism either accidental or intentional. The size allows the enclosures to house significantly sized electronic devices with space to spare. Enclosures mount to the wall enabling units to be protected in their designated location.

They have a durable finish to help protect against corrosion.

## KEY FEATURES

### General Information

- Can be used in all wiring applications as a junction, splice or power supply cabinet

### Design

- Cost effective, low maintenance and compact design.
- Continuous piano type hinge.

### Construction

- Heavy-duty enclosures are constructed with a powder coated metal to help protect against corrosion.
- Metal thickness meets or exceeds Type 1 requirements.

### Installation

- Enclosures mount to the wall enabling units to be protected in their designated location.

### Options

- Thumb or key lock (option sold separately).

### EM Models:

- Backplate (sold separately) may be mounted into cabinet.
- Back design helps accommodate uneven walls or mounting surface.
- Top, side and bottom knockouts are 1/2" and 3/4".
- Includes 1/2", 3/4", conduit knock out.
- UL, cUL Listed, Type 1 (see approvals).

### 7560 Model:

- UL Listed, Type 4.
- Includes backplate.



For more information, call 1-800-888-4784 (4STI) or visit [www.sti-usa.com](http://www.sti-usa.com)



**Safety Technology International, Inc.**

# STI Metal Protective Cabinets

## Dimensions and Technical Information

### MODELS AVAILABLE

<b>STI-7560*</b>	Metal Protective Cabinet with window
<b>STI-7561*</b>	Metal Protective Cabinet without window
<b>STI-EM07123.5</b>	Metal Protective Cabinet 18 gauge
<b>STI-EM08073.5</b>	Metal Protective Cabinet 18 gauge
<b>STI-EM111103</b>	Metal Protective Cabinet 18 gauge
<b>STI-EM111504</b>	Metal Protective Cabinet 18 gauge
<b>STI-EM121204</b>	Metal Protective Cabinet 18 gauge
<b>STI-EM151804</b>	Metal Protective Cabinet 17 gauge

### APPROVALS

- STI-7560 and STI-7561 UL Listed, Type 4
- EM models UL, cUL Listed, Type 1

Many polycarbonate cabinets also available.

\*A/C or heat options available, also available without window

Part #	H	W	D
STI-7560/STI-7561	36" (914mm)	24" (610mm)	8.79" (161mm)
STI-EM07123.5	12.20" (310mm)	7.73" (196mm)	3.84" (98mm)
STI-EM08073.5	8.40" (213mm)	7.66" (195mm)	3.80" (97mm)
STI-EM111103	11.20" (284mm)	11.28" (286mm)	3.30" (84mm)
STI-EM111504	15.20" (386mm)	11.28" (286mm)	4.30" (109mm)
STI-EM121204	12.20" (310mm)	12.7" (323mm)	4.30" (109mm)
STI-EM151804	18.20" (462mm)	15.28" (388mm)	4.30" (109mm)

### ACCESSORIES FOR EM MODELS

<b>KL544</b>	Key lock
<b>TL644</b>	Thumb lock
<b>STI-MBP0506</b>	14 gauge backplate for STI-EM07123.5 and STI-EM08073.5**
<b>STI-MBP1010</b>	14 gauge backplate for STI-EM111103 and STI-EM121204
<b>STI-MBP0913</b>	14 gauge backplate for STI-EM111504
<b>STI-MBP1316</b>	14 gauge backplate for STI-EM151804

\*\*Includes a top or bottom plate mount option



**Safety Technology  
International, Inc.**

2306 Airport Road  
Waterford, Michigan  
48327, USA

Tel: 248-673-9898  
Fax: 248-673-1246  
Toll-free: 800-888-4784  
info@sti-usa.com  
www.sti-usa.com

Unit 49G Pipers Road  
Park Farm Industrial Estate  
Redditch, Worcestershire  
B98 0HU England

Tel: 44 (0) 1527 520 999  
Fax: 44 (0) 1527 501 999  
info@sti-europe.com  
www.sti-europe.com