


Passive Twisted Pair Transmission Systems

BNC Male to Screw Terminal or BNC Male with 4" Mini coax to Screw Terminal




VC3PAIR



FRONT

BACK



TOP


SPECIFICATION	VC3PAIR
Video Input (BNC Connector)	1
Video Input Signal	1V p-p, 75 Ohms
For Use With	UTP (unshielded Twisted Pair), CAT5E, CAT6
Transmission Distance	Color: 1000 Feet B/W: 2000 Feet
Twisted Pair Output	Screw Terminal
Dimensions W x H x D	1.9" x 0.6" x 0.6"
Weight	0.7 Oz

FEATURES
◆ BNC Male to Screw Terminal for easy connection.
◆ Compact, mini size for mounting behind a DVR or Monitor.
◆ Transmits a full motion Color video signal up to 1000 feet.
◆ Passive—No power required.
◆ Eliminates the need for bulky Coaxial Cable.

Note: Specification subject to change without notice



VC4PAIR



FRONT

BACK



TOP

SPECIFICATION	VC4PAIR
Video Input (BNC Connector)	1
Video Input Signal	1V p-p, 75 Ohms
For Use With	UTP (unshielded Twisted Pair), CAT5E, CAT6
Transmission Distance	Color: 1000 Feet B/W: 2000 Feet
Twisted Pair Output	Screw Terminal
Dimensions W x H x D	0.6" x 0.6" x 5.5"
Weight	0.8 Oz

FEATURES
◆ BNC Male with 4" Mini coax to Screw Terminal for easy connection.
◆ Compact, mini size for mounting behind a DVR or Monitor.
◆ Transmits a full motion Color video signal up to 1000 feet.
◆ Passive—No power required.
◆ Eliminates the need for bulky Coaxial Cable.