

Real Time Quad / Switcher with Looping



Front Panel / Controls

SPECIFICATION	QS4L
Video Standard	NTSC / PAL - Menu Selectable
Camera Inputs / Looping Outputs	BNC x 4 Composite Video 1.0 V p-p 75 ohms BNC x 4 Composite Video 1.0 V p-p 75 ohms
Main Monitor Output	BNC x 1 Composite Video 1.0 V p-p 75 ohms
Quad Output	BNC x 1 Composite Video 1.0 V p-p 75 ohms
Resolution	720 x 480 Pixels (NTSC) / 720 x 576 (PAL)
Refresh Rate	60 Frames Per Second (NTSC) / 50 Frames Per Second (PAL)
On Screen Display	Yes
Camera Title:	On / Off - Up to 8 Characters
Time / Date:	Yes
Picture Adjust:	Contrast , Brightness, Chroma, Tint (Individual Per Camera)
Display Mode:	Date / Time (On / OFF), Channel Name (On / Off), Boundry, Input System
Power Requirement	12 Volts DC (Included)
Power Consumption	420mA , 5 Watts
Weight	1 lb 9 oz
Dimensions	8.6 " x 5.5" x 2" (W x D x H)

FEATURES

- ◆ 30 Frames Per Second Real Time Viewing
- ◆ OSD Control of All Major Functions
- ◆ Looping Video Inputs
- ◆ Time & Date Generator
- ◆ 8 Character Camera Title
- ◆ Adjustable Dwell Time
- ◆ Individual Camera Picture Adjustment
- ◆ No-Jitter Switching Mode Circuitry
- ◆ NTSC / PAL Switchable
- ◆ LED Power Indicator
- ◆ Included 12 Volt DC Power Supply

INCLUDED / ACCESSORIES

1. 12 Volt DC 500mA Power Supply
1. User Manual.

Note: Specification subject to change without notice

