

156-00264



Article Number: 156-00264

Arrowhead Mount Ties with Seal, 6.3" Long, 50lb Tensile, PA66HS, Black, 500/bag

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	156-00264
Type	T50SOSSFT6.5E-MDL
Color	Black (BK)
Features and Benefits	• Arrowhead design makes installation quick and easy by hand. • Ties "clicks" into place upon final installation signaling installer insertion is complete. • Design provides low insertion and high extraction force.
Product Description	Arrowhead Push Ties with rubber seal secure fast and easy, while providing a special rubber seal to minimize water, dirt, or dust from getting through the mounting hole. The anchor adjusts for variations in panel thicknesses which insures a secure fixing at all times.
Short Description	Arrowhead Mount Ties with Seal, 6.3" Long, 50lb Tensile, PA66HS, Black, 500/bag

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	200 N
Length L (Imperial)	6.3 "
Length L (Metric)	158.8 mm
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.6 mm
Height H (Imperial)	0.67 "
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.2 "
Bundle Diameter Max. (Metric)	30.0 mm
Disc Diameter (Imperial)	0.63 "
Disc Diameter (Metric)	16.0 mm
Panel Thickness Max. (Imperial)	0.07 "
Panel Thickness Max. (Metric)	1.8 mm
Panel Thickness Min. (Imperial)	0.02 "
Panel Thickness Min. (Metric)	0.6 mm

Mounting Hole Diameter D (Imperial)	0.25 - 0.26 "		
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm		
Mounting Hole Diameter D Min. (Imperial)	0.25 "	Mounting Hole Diameter D Max. (Imperial)	0.26 "
			Thickness T (Imperial)0.05 "
Mounting Hole Diameter D Max. (Metric)	6.7 mm		
	Mounting Hole Diameter D Min. (Metric)	6.3 mm	
Thickness T (Metric)	1.3 mm		

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	500 Pieces
Carton Quantity	3000 Pieces
Weight (Metric)	1.51 kg

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes