

156-00869



Article Number: 156-00869

Cable Tie and Edge Clip, 50lb, 6.0" Long, EC10, Panel Thickness .04"-.12", PA66UV, Black, 500/bag



Download drawing

Download spec sheet

Base Data

Local Order Number	156-00869
Type	T30REC10
Color	Black (BK)
Features and Benefits	• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
Short Description	Cable Tie and Edge Clip, 50lb, 6.0" Long, EC10, Panel Thickness .04"-.12", PA66UV, Black, 500/bag

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135 N
Length L (Imperial)	6.0 "
Length L (Metric)	150.0 mm
Length L2 (Imperial)	0.6 "
Length L2 (Metric)	15.0 mm
Fixation Method	EdgeClip, top, assembled, 2 piece
Identification Plate Position	none
Variant	Inside Serrated
Width W (Imperial)	0.14 "
Width W (Metric)	3.6 mm
Width W2 (Imperial)	0.43 "
Width W2 (Metric)	11.0 mm
Height H (Imperial)	0.04 "
Height H (Metric)	1.1 mm
Height H2 (Imperial)	0.47 "
Height H2 (Metric)	12.0 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.0 mm
Bundle Diameter Max. (Imperial)	1.4 "
Bundle Diameter Max. (Metric)	32.0 mm
Panel Thickness Max. (Imperial)	0.12 "

Panel Thickness Max. (Metric) 3.00 mm

Panel Thickness Min. (Imperial) 0.04 "

Panel Thickness Min. (Metric) 1.00 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 500

Weight (Metric) 2.3 kg

Material and Specifications

Material Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS
PA66HIRHS

ROHS Compliant Yes