

157-00036



Article Number: 157-00036

Wide Strap Cable Tie, 8 mm Stud Mount, 15.7" Length, 0.5" Wide, PA66HIRHSUV, Black, 300/pkg

RoHS

Download drawing

Download spec sheet

Base Data

Local Order Number	157-00036
Type	WSR8MM
Color	Black (BK)
Features and Benefits	• Mount provides low insertion and high extraction forces which makes for a strong and easy installation. • Clamping rails increase grip on round bundles. • Thinner strap provides increased flexibility for improved ergonomics. • Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.
Product Description	Wide Strap Heavy Duty Cable Ties features a stud mount for direction application onto a 8 mm threaded stud. The tie is 0.5" wide, and handles bundles from 0.38" - 4.2". The low profile mount design engages a minimum of 4 threads on the stud which makes it easier to apply additional mounts onto one stud.
Short Description	Wide Strap Cable Tie, 8 mm Stud Mount, 15.7" Length, 0.5" Wide, PA66HIRHSUV, Black, 300/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	120.0 lbs
Minimum Tensile Strength (Metric)	534 N
Length L (Imperial)	15.7 "
Length L (Metric)	398.8 mm
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5 "
Width W (Metric)	12.7 mm
Bundle Diameter Min. (Imperial)	0.38 "
Bundle Diameter Min. (Metric)	9.5 mm
Bundle Diameter Max. (Imperial)	4.1 "
Bundle Diameter Max. (Metric)	104.1 mm
Stud Size (Imperial)	0.315 "
Stud Size (Metric)	8.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	300 Pieces

Carton Quantity 1200

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL94 HB
Operating Temperature	-65°F to +212°F (-54°C to +100°C)
ROHS Compliant	Yes