

170-03020



Article Number: 170-03020

Fray Resistant Flame Retardant Expandable Braided Sleeveing, 1.25" Dia., Black, 50.0 ft/Standard Reel



Download drawing



Download spec sheet

Base Data

Local Order Number 170-03020

Type BSSCFR1140

Color Black (BK)

- Features and Benefits**
- Increased braid density coverage provides higher level of abrasion resistance without losing flexibility.
 - Treated yarns extinguish quickly and reduces potential flame spread to surrounding components.
 - Cuts with ordinary scissors without fraying ends.

Product Description Treated polyester yarns that can be cut with sharp scissors and provides flame retardant properties. Well suited for situations where access to a hot knife is either impractical or impossible. Contains white tracer thread for easy identification.

Short Description Fray Resistant Flame Retardant Expandable Braided Sleeveing, 1.25" Dia., Black, 50.0 ft/Standard Reel

Product Dimensions

Length L (Imperial) 50.0 ft

Length L (Metric) 15.2 m

Reel Length (imperial) 50.0 ft

Bundle Diameter Min. (Imperial) 1.0 "

Bundle Diameter Min. (Metric) 25.4 mm

Bundle Diameter Max. (Imperial) 1.5 "

Bundle Diameter Max. (Metric) 38.1 mm

Nominal Diameter (Imperial) 1-1/4 "

Nominal Diameter (Metric) 31.8 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 50 ft

Weight (Metric) 0.35 kg

Weight (imperial) 0.78 lbs

Material and Specifications

Material Polyester (PET)

Material Shortcut PET

Flammability UL VW-1
Mil-202

Operating Temperature -94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

UL Recognized (US and Canada) Yes