

170-03027



Article Number: 170-03027

Polyamide (PA66) Monofilament Expandable Braided Sleeving, 0.5" Dia., Black, 100.0 ft/Standard Reel



Download drawing



Download spec sheet

Base Data

Local Order Number 170-03027

Type BSPA66120

Color Black (BK)

Features and Benefits

- Nylon monofilament construction weave offers a tight, 12 mil braid that provides full coverage but will not rot or retain moisture.
- Material performs well in wet applications and where abiding substrate has a smooth surface.

Product Description A pliable yet durable nylon sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.

Short Description Polyamide (PA66) Monofilament Expandable Braided Sleeving, 0.5" Dia., Black, 100.0 ft/Standard Reel

Product Dimensions

Length L (Imperial) 100.0 ft

Length L (Metric) 30.48 m

Reel Length (imperial) 100.0 ft

Bundle Diameter Min. (Imperial) 0.375 "

Bundle Diameter Min. (Metric) 9.5 mm

Bundle Diameter Max. (Imperial) 0.75 "

Bundle Diameter Max. (Metric) 19.1 mm

Nominal Diameter (Imperial) 1/2 "

Nominal Diameter (Metric) 12.7 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 100 ft

Weight (Metric) 0.47 kg

Weight (imperial) 1.03 lbs

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability non flammable

Operating Temperature -49°F to +302°F (-45°C to +150°C)

ROHS Compliant Yes

