

170-03047



Article Number: 170-03047

Polyamide (PA66) Monofilament Expandable Braided Sleeving, 0.75" Dia., Black, 250.0 ft/Bulk Reel

 **RoHS**

 [Download drawing](#)

 [Download spec sheet](#)

Base Data

Local Order Number	170-03047
Type	BSPA66340B
Color	Black (BK)
Features and Benefits	- Nylon monofilament construction weave offers a tight, 12 mil braid that provides full coverage but will not rot or retain moisture. - Material performs well in wet applications and where abiding substrate has a smooth surface.
Product Description	A pliable yet durable nylon sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.
Short Description	Polyamide (PA66) Monofilament Expandable Braided Sleeving, 0.75" Dia., Black, 250.0 ft/Bulk Reel

Product Dimensions

Length L (Imperial)	250.0 ft
Length L (Metric)	76.2 m
Reel Length (imperial)	250.0 ft
Bundle Diameter Min. (Imperial)	0.5 "
Bundle Diameter Min. (Metric)	12.7 mm
Bundle Diameter Max. (Imperial)	1.25 "
Bundle Diameter Max. (Metric)	31.8 mm
Nominal Diameter (Imperial)	3/4 "
Nominal Diameter (Metric)	19.1 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	250 ft
Weight (imperial)	3.68 lbs
Weight (Metric)	1.67 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	non flammable
Operating Temperature	-49°F to +302°F (-45°C to +150°C)
ROHS Compliant	Yes

