

170-03054



Article Number: 170-03054

Aluminum Laminated Fiberglass Sleeve Tube, 1/2" Dia., Silver, 250ft/Bulk Reel

 RoHS

-  Download drawing
-  Download spec sheet
-  Download tech sheet

Base Data

Local Order Number	170-03054
Type	BSHTTST12SRB
Color	Silver (SR)
Features and Benefits	• A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion. • Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments. • Cuts with ordinary scissors for fast, easy application.
Product Description	A tubular shaped sleeving product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to deflect radiant heat away from sensitive components inside the tube.
Short Description	Aluminum Laminated Fiberglass Sleeve Tube, 1/2" Dia., Silver, 250ft/Bulk Reel

Product Dimensions

Length L (Imperial)	250.0 ft
Length L (Metric)	76.2 m
Reel Length (imperial)	250.0 ft
Bundle Diameter Max. (Imperial)	0.437 "
Bundle Diameter Max. (Metric)	11.1 mm
Diameter D (imperial)	0.5 "
Diameter D (metric)	12.7 mm
Nominal Diameter (Imperial)	1/2 "
Nominal Diameter (Metric)	12.7 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	1
Package Quantity (Metric)	1
Carton Quantity	1
Weight (Metric)	2.90 kg
Weight (imperial)	6.375 lbs

Material and Specifications

Material	Glass fiber with aluminium foil (GF-AL)
Material Shortcut	GF-AL
Flammability	non flammable

Operating Temperature -76°F to +491°F (-60°C to +255°C)

ROHS Compliant Yes