



170-03065



Article Number: 170-03065

Aluminum Laminated Fiberglass Sleeve, 1.75" Dia., Silver, 50.0 ft/Standard Reel

 RoHS

 Download drawing

 Download spec sheet

 Download tech sheet

Base Data

Local Order Number	170-03065
Type	BSHTTST134SR
Color	Silver (SR)
Features and Benefits	<ul style="list-style-type: none"><li>• A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.</li><li>• Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.</li><li>• Cuts with ordinary scissors for fast, easy application.</li></ul>
Product Description	A tubular shaped sleeving product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to deflect radiant heat away from sensitive components inside the tube.
Short Description	Aluminum Laminated Fiberglass Sleeve, 1.75" Dia., Silver, 50.0 ft/Standard Reel

Product Dimensions

Length L (Imperial)	50.0 ft
Length L (Metric)	15.2 m
Reel Length (imperial)	50.0 ft
Bundle Diameter Max. (Imperial)	1.687 "
Bundle Diameter Max. (Metric)	42.8 mm
Nominal Diameter (Imperial)	1-3/4 "
Nominal Diameter (Metric)	44.5 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	50 ft
Package Quantity (Metric)	1
Weight (imperial)	3.70 lbs
Weight (Metric)	1.68 kg

Material and Specifications

Material	Glass Fiber (GF) Aluminium (AL)
Flammability	non flammable
Operating Temperature	-76°F to +491°F (-60°C to +255°C)
ROHS Compliant	Yes

