


170-03085



Article Number: 170-03085

Split Wrap Braided Sleeving, 1.0" ID, PET, Orange, 100.0 ft/Bulk Reel

 **RoHS**

 [Download drawing](#)

 [Download spec sheet](#)

Base Data

Local Order Number	170-03085
Type	BSPSW103B
Color	Orange (OG)
Features and Benefits	• Split wrap design installs quickly, saving assembly time and future accessibility without disassembly. • Unique construction retains shape and rigidity throughout unrolling. • Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.
Product Description	A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.
Short Description	Split Wrap Braided Sleeving, 1.0" ID, PET, Orange, 100.0 ft/Bulk Reel

Product Dimensions

Length L (Imperial)	100.0 ft
Length L (Metric)	30.48 m
Reel Length (imperial)	100.0 ft
Bundle Diameter Max. (Imperial)	1.0 "
Bundle Diameter Max. (Metric)	25.4 mm
Nominal Diameter (Imperial)	1 "
Nominal Diameter (Metric)	25.4 mm

Logistics and Packaging

Quantity Per	box
Package Quantity	100 ft
Package Quantity (Metric)	100.0 ft
Weight (Metric)	0.91 kg
Weight (imperial)	2.0 lbs

Material and Specifications

Material	Polyester (PET)
Material Shortcut	PET
Flammability	UL94 V0
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
ROHS Compliant	Yes

UL Recognized (US and Canada) Yes