

170-03093



Article Number: 170-03093

Flame Retardant Expandable Braided Sleeving, 1.0" Dia., Black, 250.0 ft/Bulk Reel

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	170-03093
Type	BSPFR100B
Color	Black (BK)
Features and Benefits	• Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required. • Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.
Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.
Short Description	Flame Retardant Expandable Braided Sleeving, 1.0" Dia., Black, 250.0 ft/Bulk Reel

Product Dimensions

Length L (Imperial)	250.0 ft
Length L (Metric)	76.2 m
Reel Length (imperial)	250.0 ft
Bundle Diameter Min. (Imperial)	0.625 "
Bundle Diameter Min. (Metric)	15.9 mm
Bundle Diameter Max. (Imperial)	1.625 "
Bundle Diameter Max. (Metric)	41.3 mm
Nominal Diameter (Imperial)	1 "
Nominal Diameter (Metric)	25.4 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	250 ft
Package Quantity (Metric)	250.0 ft
Weight (Metric)	1.5 kg
Weight (imperial)	3.4 lbs

Material and Specifications

Material	Polyester (PET)
Material Shortcut	PET
Flammability	FMVSS 302 VW-1

FAR 25
Mil-202

Operating Temperature -94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

Certification/Specification UL94

UL Recognized (US and Canada) Yes