

170-03111



Article Number: 170-03111

Plenum Rated Expandable Braided Sleeving (Halar), 1.25" Dia., White, 50.0 ft/Reel

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	170-03111
Type	BSHLR11410
Color	White (WH)
Features and Benefits	• Meets UL 2024 and NFPA 262 specifications meets requirements for use in plenum applications. • Technically advanced monofilament material is rated as low smoke, flame resistant and can withstand exposure to Cobal 60 radiation. • Exceeds requirements of FMVSS 302 as well as aviation industry requirements of FAR25.
Product Description	Halar self-extinguishing sleeving is used where flammability, high temperature endurance and low outgassing are the primary concern.
Short Description	Plenum Rated Expandable Braided Sleeving (Halar), 1.25" Dia., White, 50.0 ft/Reel

Product Dimensions

Length L (Imperial)	50.0 ft
Length L (Metric)	15.2 m
Reel Length (imperial)	50.0 ft
Bundle Diameter Min. (Imperial)	0.75 "
Bundle Diameter Min. (Metric)	19.1 mm
Bundle Diameter Max. (Imperial)	1.75 "
Bundle Diameter Max. (Metric)	44.5 mm
Nominal Diameter (Imperial)	1-1/4 "
Nominal Diameter (Metric)	31.8 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	50 ft
Weight (Metric)	0.59 kg
Weight (imperial)	1.3 lbs

Material and Specifications

Material	Polyamide 6.6 (E/CTFE)
Material Shortcut	E/TFE
Flammability	UL VW-1 FAR 25
Operating Temperature	-103°F to +302°F (-75°C to +150°C)

ROHS Compliant Yes

Certification/Specification UL2024

UL Recognized (US and Canada) Yes