

170-03112



Article Number: 170-03112

Plenum Rated Expandable Braided Sleeving (Halar), 1.75" Dia., Black, 30.0 ft/Reel



Download drawing



Download spec sheet

Base Data

Local Order Number	170-03112
Type	BSHLR1340
Color	Black (BK)

- Features and Benefits**
- Meets UL 2024 and NFPA 262 specifications meets requirements for use in plenum applications.
 - Technically advanced monofilament material is rated as low smoke, flame resistant and can withstand exposure to Cobal 60 radiation.
 - Exceeds requirements of FMVSS 302 as well as aviation industry requirements of FAR25.

Product Description Halar self-extinguishing sleeving is used where flammability, high temperature endurance and low outgassing are the primary concern.

Short Description Plenum Rated Expandable Braided Sleeving (Halar), 1.75" Dia., Black, 30.0 ft/Reel

Product Dimensions

Length L (Imperial) 30.0 ft

Length L (Metric) 9.1 mm

Reel Length (imperial) 30.0 ft

Bundle Diameter Min. (Imperial) 1.25 "

Bundle Diameter Min. (Metric) 31.8 mm

Bundle Diameter Max. (Imperial) 2.75 "

Bundle Diameter Max. (Metric) 69.9 mm

Nominal Diameter (Imperial) 1-3/4 "

Nominal Diameter (Metric) 44.4 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 30 ft

Package Quantity (Metric) 30.0 ft

Weight (imperial) 1.32 lbs

Weight (Metric) 0.60 kg

Material and Specifications

Material Polyamide 6.6 (E/CTFE)

Material Shortcut E/TFE

Flammability UL VW-1
FAR 25

Operating Temperature -103°F to +302°F (-75°C to +150°C)

ROHS Compliant Yes

Certification/Specification UL2024

UL Recognized (US and Canada) Yes