

170-03116



Article Number: 170-03116

Fray Resistant Flame Retardant Expandable Braided Sleeving, 0.13" Dia., Black, 1000.0 ft/Bulk Reel

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	170-03116
Type	BSSCFR180B
Color	Black (BK)
Features and Benefits	• Increased braid density coverage provides higher level of abrasion resistance without losing flexibility. • Treated yarns extinguish quickly and reduces potential flame spread to surrounding components. • Cuts with ordinary scissors without fraying ends.
Product Description	Treated polyester yarns that can be cut with sharp scissors and provides flame retardant properties. Well suited for situations where access to a hot knife is either impractical or impossible. Contains white tracer thread for easy identification.
Short Description	Fray Resistant Flame Retardant Expandable Braided Sleeving, 0.13" Dia., Black, 1000.0 ft/Bulk Reel

Product Dimensions

Length L (Imperial)	1000.0 ft
Length L (Metric)	304.8 m
Reel Length (imperial)	1000.0 ft
Bundle Diameter Min. (Imperial)	0.125 "
Bundle Diameter Min. (Metric)	3.2 mm
Bundle Diameter Max. (Imperial)	0.25 "
Bundle Diameter Max. (Metric)	6.4 mm
Nominal Diameter (Imperial)	1/8 "
Nominal Diameter (Metric)	3.3 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	1000 ft
Weight (Metric)	1.8 kg
Weight (imperial)	4.00

Material and Specifications

Material	Polyester (PET)
Material Shortcut	PET
Flammability	Mil-202 UL VW-1
Operating Temperature	-94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

UL Recognized (US and Canada) Yes