

170-03136



Article Number: 170-03136

Split Wrap Braided Sleeving, 1.0" ID, PET, Black, 400.0 ft/Large Bulk Reel



Download drawing



Download spec sheet

Base Data

Local Order Number 170-03136

Type BSPSW100LB

Color Black (BK)

Features and Benefits

- Split wrap design installs quickly, saving assembly time and future accessibility without disassembly.
- Unique construction retains shape and rigidity throughout unrolling.
- Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.

Product Description A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.

Short Description Split Wrap Braided Sleeving, 1.0" ID, PET, Black, 400.0 ft/Large Bulk Reel

Product Dimensions

Length L (Imperial) 400.0 ft

Length L (Metric) 121.9 m

Reel Length (imperial) 400.0 ft

Bundle Diameter Max. (Imperial) 1.0 "

Bundle Diameter Max. (Metric) 25.4 mm

Nominal Diameter (Imperial) 1 "

Nominal Diameter (Metric) 25.4 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 400 ft

Package Quantity (Metric) 400.0 ft

Weight (Metric) 3.6 kg

Weight (imperial) 8.0 lbs

Material and Specifications

Material Polyester (PET)

Material Shortcut PET

Flammability UL94 V0

Operating Temperature -94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

UL Recognized (US and Canada) Yes

© HellemanTyton 2015