

170-03175



Article Number: 170-03175

Aluminum Laminated Fiberglass Sleeve, 0.38" Dia., Silver, 100.0 ft/Standard Reel



 Download drawing

 Download spec sheet

 Download tech sheet

Base Data

Local Order Number	170-03175
Type	BSHTTST38SR
Color	Silver (SR)
Features and Benefits	<ul style="list-style-type: none">• A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.• Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.• Cuts with ordinary scissors for fast, easy application.
Product Description	A tubular shaped sleeving product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to deflect radiant heat away from sensitive components inside the tube.
Short Description	Aluminum Laminated Fiberglass Sleeve, 0.38" Dia., Silver, 100.0 ft/Standard Reel

Product Dimensions

Length L (Imperial)	100.0 ft
Length L (Metric)	30.48 m
Reel Length (imperial)	100.0 ft
Bundle Diameter Max. (Imperial)	0.437 "
Bundle Diameter Max. (Metric)	11.1 mm
Diameter D (imperial)	0.38 "
Diameter D (metric)	9.7 mm
Nominal Diameter (Imperial)	3/8 "
Nominal Diameter (Metric)	9.7 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	100 ft
Package Quantity (Metric)	1
Reel Weight (Metric)	1.02 kg
Reel Weight (Imperial)	2.25 lbs

Material and Specifications

Material	Glass Fiber (GF) Aluminium (AL)
Flammability	non flammable
Operating Temperature	-76°F to +491°F (-60°C to +255°C)

