


170-03203



Article Number: 170-03203

Heavy Duty Woven Sleeve, 1" Dia., Nylon, Black, 50ft/Reel

 RoHS

 Download spec sheet

 Download tech sheet

Base Data

Local Order Number	170-03203
Type	BSHDWV
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none">• Tightly woven fabric bundles and protects cables and hoses from sunlight and abrasion damage; also deflects high pressure hose ruptures.• Nylon material resists gasoline, salt and other chemicals.• Cut to size easily with regular scissors.
Product Description	Sleeving made of a tightly woven nylon fabric, slides onto hoses, cables and components to protect them from abrasion and environmental elements, including UV damage. Also protects surrounding surfaces from damage.
Short Description	Heavy Duty Woven Sleeve, 1" Dia., Nylon, Black, 50ft/Reel

Product Dimensions

Length L (Imperial)	50.0 ft
Length L (Metric)	15.24 m
Reel Length (imperial)	50.0 ft
Diameter D (imperial)	1 "
Diameter D (metric)	25.4 mm
Nominal Diameter (Imperial)	1 "
Nominal Diameter (Metric)	25.4 mm
Wall Thickness WT (Imperial)	0.045 "
Wall Thickness WT (Metric)	1.14 mm

Logistics and Packaging

Quantity Per	box
Package Quantity	50.0 ft
Package Quantity (Metric)	50
Carton Quantity	50.0 ft

Material and Specifications

Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	non flammable
Operating Temperature	-49°F to +248°F (-45°C to +120°C)
ROHS Compliant	Yes

